



## SST-3台式石英停秒钟使用说明书

### 特征说明

沙逊SST-3指针式石英停秒钟是学校，运动，实验和工业的精确计时工具。更是中小学实验室必备仪器，经由特殊精确设计，计时器牢固稳定，非常易于辨识的刻度表盘以及夜光功能。

### 主要技术数据

钟面显示：外圈刻度 0-60秒±0-60秒

内圈刻度 0-100/100分钟

尺寸：132\*95\*173mm

电池：1.5V 5号碱性电池一节

功能：开始/停止/重启 以及复零功能


### 使用方法

准备：移除位于钟底部的后盖，放入一节碱性5号电池(LR6 AA)。

1 开始/停止：按红色按钮 **START/STOP**

复零：按灰色按钮 **RESET**

2 重复计时：机器在正常计时下，按灰色键复零后自动重新计时。



上海沙逊钟表有限公司  
 地址:上海市长宁路1277弄25号301室  
 电话:021-52410333、52410222  
 传真:021-52418077  
 E-mail:shaxun@sasey.com.cn  
 邮编:200051

## Quartz table stopclock

### Preparation

Remove the battery-cover located under the base, when changing the battery type AA of 1.5V, reposit polarity.

Replace battery cover, reset the stopclock by pressing the black button.

### Functions

1 start: press the red button

stop: press the red button

reset: press the black button

2 additional: press the red button consecutively as often as required

3 tempo: start-reset with automatic starting of the second hand-press red button and then the black one as often as requested.

### Technical data

movement: quartz controlled 32768Khz

accuracy: +/- 1s/month

start: second hand 60sec.-100/100min

time units: 1sec and 1/100 min.

case: ABS, 132\*95\*173mm

weight: 370g

battery: 1.5V alkaline AA (LR6)

temperature in use: -10°C to 60°C

